

ROITHNER LASERTECHNIK GmbH

TEL. +43 | 586 52 43 -0, FAX. -44 OFFICE@ROITHNER-LASER.COM



v 3.0

UV-TIAMO-BL

- Broadband UVA+UVB+UVC amplified SiC UV detector
- **Integrated Transimpedance Amplifier**
- Sensitivity Range: 221-358 nm
- Approx. max irradiance 18nW/cm²
- TO5 housing with concentrator lens cap
- Applications: very low UV radiation detection, flame detection



Description

The UV-TIAMO devices are using modern hybride technology to cancel unwanted signal disturbances caused by moisture or electromagnetic radiation. The stable 0...5V output voltage can be directly connected to a SPC controller or a voltage multimeter. No external amplifier is needed.

The photodetectors work with a SiC sensing chip. SiC provides the unique property of extreme radiation hardness, near-perfect visible blindness, low dark current, high speed and low noise. These features make SiC the best available material for visible blind semiconductor UV detectors.

Maximum Ratings (T = 25°C)

Davamatav	Cymphol	Val	Heit	
Parameter	Symbol	Min.	Max.	Unit
Operating Temperature	T _{opr}	-25	+85	°C
Storage Temperature	T _{stg}	-40	+100	°C
Soldering Temperature (max. 3s)	T _{sol}		+300	°C

General Characteristics (T= 25°C)

Davamatav	Cumbal	Values			Harit
Parameter	Symbol	Min.*	Тур.*	Max.*	Unit
Supply voltage	V _{supply}	2.5		5.0	V
Saturation voltage	V_{sat}		V _{supply} - 5%		V
Dark offset voltage	V_{offset}		50		μV
Current consumption	1		150		μΑ
Bandwidth (-3 dB)	Θ		15		Hz
Risetime (10-90%) (other risetimes on demand)	t _{rise}		0,182		s
Temperature coefficient	T _C			-0.3	%/K

Spectral Characteristics (T = 25°C)

Doromotor	Cumbal	Values			Unit
Parameter	Symbol	Min.*	Тур.*	Max.*	Unit
Sensitivity at peak	S _{max}		280		mV/nW/cm ²
Wavelength of max. spectral sens.	λ_{max}		280		nm
Sensitivity range (S=0.1*S _{max})	-	221		358	nm
Visible blindness (S _{max} / S _{>405nm})	VB		10 ¹⁰		-

www.roithner-laser.com





ROITHNER LASERTECHNIK GmbH

WIEDNER HAUPTSTRASSE 76 IO40 VIENNA AUSTRIA TEL. +43 I 586 52 43 -0, FAX. -44 OFFICE@ROITHNER-LASER.COM



Performance Characteristics





Product Portfolio

We offer the following amplified UV photodetectors:

Option	Approx. min irradiance	Approx. max irradiance (V _{supply} = 5V)
UV-TIAMO-BL	1.8 pW/cm ²	18 nW/cm ²
UV-TIAMO	1.8 nW/cm ²	18 μW/cm ²
UV-TIAMO-S	1.8 µW/cm ²	18 mW/cm ²
UV-TIAMO-M	18 µW/cm ²	180 mW/cm ²


UV photodiodes without amplifier and different spectral sensitivities are available.

Falls benötigt

Falls benötigt...


www.roithner-laser.com 2

Outline Dimensions



All dimensions in mm

Connection diagram



Application Note

To make the photodiode running reliably, particularly in harsh environment, EMC compatibility and protection against dust, water, and mechanical influences is required. Below listed modules base on a SiC photodiode and guarantee this protection and safety.

UV-probe: SiC based sensor modules in **customizable industry grade housings** (e.g. cosine response, water pressure proof, sapphire windows) and **different electronic output configurations** (voltage, current, USB, Can, LAN) to choose from.

→ Ask us for further details!

© All Rights Reserved

The above specifications are for reference purpose only and subjected to change without prior notice

www.roithner-laser.com 3